# **ALL ABOUT ACCU-THERM®**





# **Paul Mueller Company**

#### Mueller® is Your Heat Transfer Solutions Provider!

For over half a century, Paul Mueller Company has been building a reputation as an outstanding manufacturer of stainless steel tanks and industrial processing equipment that make the customer's process smoother, faster, and more reliable. Since our inception in 1940, we have evolved from a small-scale fabricator into a global process solution provider with over 60 years of success in heat transfer applications. We offer manufactured equipment and components, integrated process systems, and expanded scope construction.

Mueller® products are used in over 100 countries worldwide in a wide variety of industrial applications, including heat transfer; HVAC; heat recovery; food, dairy, and beverage processing; pharmaceutical, biotechnological, and chemical processing; water distillation; process cooling; thermal energy storage; and on dairy farms. Mueller is uniquely qualified to handle large and complex fluid handling systems from project concept through installation. We also offer modular fabrication, field construction, maintenance and repair, and complete turnkey project execution. Mueller delivers outstanding equipment and unique solutions to the process industries with our technical expertise, innovative engineering, and manufacturing resources.

**Worldwide representation.** Paul Mueller Company heat transfer products are supported by a worldwide network of factory trained representatives with thorough, up-to-date product knowledge ensuring rapid response to your inquiries.

**Factory technicians and field service available.** Our trained personnel offer rapid response to your service needs.

**Mueller Field Operations, Inc.** Our field construction capabilities allow us to build onsite, offering our customers more versatility and flexibility.

**Mueller Transportation, Inc.** allows us to provide you with competitive delivery rates on standard products. MTI offers dedicated handling for large or critical delivery items and are able to work with you directly to resolve any transportation issues.

We are committed to meeting and exceeding our customers' expectations of value by providing high quality equipment, excellent service, and complete process solutions.



#### Worry-Free, Highly Efficient Heat Transfer Performance

Mueller Accu-Therm® plate heat exchangers are designed to provide you worry-free, highly efficient heat transfer performance — whether you are processing simple fluids, viscous solutions, or particulates.

The advantages of the Mueller Accu-Therm plate heat exchanger (PHE) begins with its design. PHEs offer greater efficiency, lower cost, closer approach temperatures, and easier cleaning and maintenance than other heat transfer technologies. In comparison to shell-and-tube heat exchangers, plate heat exchangers of similar capacity require only one-fifth to one-half the floor space and are easy to expand. An Accu-Therm stands apart from the rest with its wide array of plate sizes and corrugation patterns. We can custom build your Mueller Accu-Therm PHE to suit your individual application and heat transfer requirements.



## How Does the Mueller Accu-Therm Work?

Mueller Accu-Therm plate heat exchangers provide more efficient heat transfer by design. An Accu-Therm consists of a series of embossed heat transfer plates with gaskets around the perimeter of every plate to contain pressure and control the flow of each medium. They can be designed for multiple fluids or thermal requirements in a single frame.

The gasketed plates are assembled in a pack, mounted on upper and lower guide rails, and compressed between two end frames with compression bolts. Fluids enter and exit the Accu-Therm through end-frame connections and are distributed to the plates through portholes in the plates.


The flow to individual passages between plates is controlled by alternate placement of port gaskets. Within the heat exchanger, the fluid to be heated (or cooled) flows down one side of each plate, while the heating (or cooling) medium flows in the opposite direction on the other side of the plate.

The temperature difference created by these opposite flows results in the closest possible approach temperature for maximum heat transfer efficiency.

While hot and cold fluids flow in opposite directions across a single plate, the flow pattern between plates can vary. Plate heat exchanger flow patterns can be single- or multi-pass. A single-pass arrangement means each fluid flows in the same respective direction across

all the plates in the unit. A multipass arrangement is designed so fluids can change their respective flow directions.

Single-pass units are suitable for most applications, but extremely close approach temperatures or large temperature differences may call for a multi-pass configuration.



Every Mueller Accu-Therm unit receives rigorous quality inspections for leaks and pressure capabilities. If your plate heat exchanger does not operate according to your exact order specifications, our factory service technicians will make the necessary adjustments immediately.

#### Accu-Therm® Applications

## **Applications**

#### **Automotive**

 Cooling tower isolation, hydraulic oil coolers, induction heater cooling, paint heating, phosphate tank heaters, plating solution cooling, quench oil heat exchangers, seal water coolers, and welder water cooling.

#### **Brewing**

 Brine cooling, water heating, and wort cooling.

#### Caustic Soda

 Acid coolers, brine heaters and coolers, caustic coolers, and hydrogen gas coolers.

#### Chemical

 Acid heating and cooling, brine heating and cooling, condensers, gas scrubber heaters, process interchangers, and process water isolation.

#### Food

 Corn syrup cooling, edible-oil heaters and coolers, fructose solution heating and cooling, starch heaters and coolers, sugar refining, whiskey recuperators, and yeast coolers.

#### **HVAC**

 Condenser water heat recovery, cooling tower isolation, district heating and cooling, engine cooling, free cooling, fuel oil heating, generator cooling, geo-thermal heating, heat pump systems, heating water with steam, lube oil cooling, seawater isolation, and thermal storage systems.

#### Marine

• Seawater isolation/exchanger.

#### Metal Working

 Anodizer heaters and coolers, pickling tank heating, plating heaters and coolers, quench oil coolers, and strike solution cooling.

#### Petroleum

 Natural gas processing, offshore drilling, oil refining, and petrochemical processing.

#### Power

 Auxiliary cooling circuit isolation, condenser water isolation, cogeneration applications, diesel engine cooling and heat recovery, geothermal applications, lubrication oil cooling, and refuse burning applications.

#### Pulp and Paper

 Blow-down liquor coolers, boiler blow-down heat recovery, caustic soda coolers, digester heaters, and white water and black liquor heating.

#### Steel

 Cooling of continuous casting installations, hydraulic oil cooling, jacket water coolers, mold water cooling, refractory liner cooling, roll oil cooling, scrubber coolers, and slab induction heating coolers.

#### **Textile**

 Caustic solution heating and cooling, dye concentrate heating, heat recovery, and washers.



A Mueller Accu-Therm skid mounted in an oil drilling rig's brake cooling package for an onshore platform.



A mixing skid, complete with a stainless steel Accu-Therm, used for processing liquor.



An Accu-Therm used in a heating and cooling system.

#### Accu-Therm Features and Benefits

## **Features and Benefits**

#### Close Approach Temperatures

 Approach temperatures of 2 to 3°F are possible because of the true counterflow and high heat transfer efficiency of the plates.

#### Compact and Lightweight

- Requires <sup>1</sup>/<sub>5</sub> to <sup>1</sup>/<sub>2</sub> less floor space than other types of heat transfer equipment.
- Lighter in total weight than other heat exchangers because of reduced liquid volume and the more efficient surface area for a given application.

#### Connections

- Studded ports are standard and can be fully lined to protect against erosion and corrosion of the frame.
- Lap-joint, weld-neck, ferrule, and victaulic connections are also available.
- Connections can be mixed and matched to suite individual needs.

#### Cross Contamination Eliminated

- · Each medium is individually gasketed.
- The space between gaskets is vented to atmosphere.

#### Easy to Inspect and Clean

- Simply remove the compression bolts and slide away the moveable end frame to inspect 100% of the Accu-Therm heat transfer surface.
- Easy and economical to clean-in-place (CIP).

#### Expandable

 Adjust the unit's thermal performance by adding or removing plates.

#### Extensive Selection

- Heat transfer surface areas from 0.5 to 51 square feet.
- Multiple embossed patterns.
- Exclusive "free-flow" plate design.

#### Frame Assembly

- Heavy-duty construction.
- Optimum plate pack compression and leak prevention.

#### Gaskets

- Designed to positively locate in gasket grooves.
- Lock-in feature available on most models.



Larger Accu-Therm frames have roller bearing support on the moveable frame for ease of assembly.



Lock-in gaskets speed the assembly process. They can be replaced during shutdown — saving you time and money.

#### Highly Efficient Heat Transfer Performance

- "U" values of 1,500 and greater are possible!
- Accu-Therm plates promote high turbulence at low fluid velocities.
- High turbulence results in very high heat transfer coefficients.

#### High Flow Rates

- Flows up to 24,000 gpm.
- Port diameters up to 20".

#### Inspection and Testing

- Rigorous quality assurance inspections.
- Each circuit independently tested at full design pressure.
- ASME registration available.

#### Lower Cost

 More economical than other types of heat exchangers due to the higher thermal efficiency and lower manufacturing costs.

#### Multiple Duties with a Single Unit

• Heat or cool two or more fluids within the same unit by installing intermediate divider sections.

#### More Heat Transfer Surface

• Up to 25,000 square feet (2,323 square meters) of heat transfer surface in a single exchanger.

#### Reduced Fouling


 High turbulence, uniform fluid distribution, smooth plate surface, and high shear stresses reduce fouling.

#### **Shrouds**

 Optional OSHA-approved plate pack shrouds are available in attractive and durable embossed aluminum or 2B stainless steel to protect personnel.



Compression bolts are zinc coated for effective corrosion resistance and are mechanically locked into place on medium-to-large units.



Closeup of Accu-Therm plates mounted on a unit's lower guide rail.

#### Varieties of Accu-Therm

## **Plate Designs**

Accu-Therm plates are available in several different corrugation patterns for various heat transfer effects. Your Mueller representative will recommend the best plate or plate combination for your needs.

#### Horizontal (H)

Horizontal herringbone embossing. Highest heat transfer coefficients and pressure drop.

#### Combination (H/V)


A combination of H and V plates for an intermediate range of heat transfer co-efficients and pressure drop.

#### Vertical (V)

Vertical herringbone embossing. Slightly lower heat transfer coefficients and pressure drop.

#### Special Performance (F, G, & P)

Special plate geometries for custom heat transfer needs.



## **Innovative "Free-Flow" Plate Design**

Mueller also offers the expandable, lightweight Accu-Therm "Free-Flow" plate heat exchanger, which features a clever heat transfer plate designed with a more open fluid-flow channel, making it ideal for viscous products, slurries, and effluent streams that contain particles and fibers which can block the flow channels and plug up conventional heat exchangers.

Each medium is individually gasketed in the "Free-Flow" plate heat exchanger, making it ideal for applications where product contamination cannot be tolerated.

In addition, these compact units are easy to disassemble and clean, which means less downtime and cost during maintenance.



# **Frame Types**

#### **B** Frame

B frames are for larger units or for applications where it is desirable to have heat transfer plates hanging from the upper guide bar.

#### C Frame

These compact, cantilevertype frames are ideal for use where space is limited.

#### F Frame

Intermediate-size frame.



# **Materials of Construction**

#### **Plates**

- 304 and 316 stainless steel
- Titanium
- Avesta SMO 254®
- Hastelloy®
- Nickel
- Incoloy®

#### Gaskets

- Nitrile® (NBR)
- Ethylene propylene rubber (EPDM)
- Silicone
- Viton®
- Butyl (resin cured)



#### Varieties of Accu-Therm

## **Double-Wall Plate Heat Exchanger**

Mueller's double-wall Accu-Therm plate heat exchanger is constructed with two identical plates nested together. Each of the double-wall pairs are fully welded or uniquely gasketed at the port locations, creating a two-layer heat transfer wall. The double-wall pairs are then assembled into the heat exchanger in the same way single plates are installed.

In the unlikely event that your product might penetrate through one of the plates, the fluid exits between the two plates at the edge of the unit. This allows for immediate visual monitoring of the unit in addition to providing maximum protection against mixing of the products. As with every standard Accu-Therm design, any gasket failure also permits the leaking fluid to be safely diverted to the edge of the plate pair. Again, this allows for immediate detection and security that the fluids are not mixing.

Applications include acid heating and cooling, potable water heat exchangers, lubricating oil coolers, transformer oil coolers, quench oil cooling, and any process that demands the highest security from mixing of the two fluids.

The double-wall Accu-Therm plate heat exchanger has all of the features of the standard design, with only a small impact on thermal efficiency by adding the second wall of the plate pair.





# **Semi-Welded Plate Heat Exchanger**

The plate pack in the semi-welded plate heat exchanger is built utilizing welded cassettes (two plates welded together). The refrigerant side is contained within the welded portion of the cassette to include welding of the fluid port. Gaskets seal the secondary side, which makes the plate pack easy to disassemble and clean. The welded cassettes are designed for optimum gasket sealing. Higher pressure improves the sealing of the gaskets.

The Mueller semi-welded Accu-Therm plate heat exchanger/evaporator is ideal for fluid chilling in refrigeration applications.



## **Custom Designing Your Accu-Therm PHE**

For assistance with custom designing a heat exchanger, contact your Mueller representative or call 1-800-MUELLER for the representative nearest you. You'll be asked to complete the following chart. Our engineers will then figure the exact plate size and channel configuration you'll need. Submit your applications through our Web site at www.muel.com or www.hxrx.com or call us at 1-800-MUELLER (683-5537).

	HOT SIDE	COLD SIDE
Fluid Circulated		
Flow Rate, gpm		
Temperature In, °F		
Temperature Out, °F		
Max. Allowable Working Temperature, °F		
Operating Pressure, psig		
Max. Allowable Working Pressure, psig		
Max. Pressure Drop, psi		
Specific Heat		
Specific Gravity		
Density		
Viscosity		
Thermal Conductivity		
Required Gasket Material		
Required Plate Material		
ASME Code Requirements		

## **Need More Info?**

Complete detailed information on the installation, operation, and maintenance of the Accu-Therm plate heat exchanger is available in our instruction manual, Part No. 9804186.

Call 1-800-Mueller to request a copy or visit our Web site at www.hxrx.com.



### Mueller Quality Delivered Right to Your Door

## **On-Time Delivery**

Paul Mueller Company has one of the best on-time shipping records in the industry! Shipment of equipment with complex specifications often takes less than four weeks.

Our "Quick Ship" program is available on some units with shipment in just 3-5 days.







## Mueller Offers Heat Transfer for Every Part of Your Process!

You will find solutions to every heat transfer need within our specialized product lines. In addition to Accu-Therm plate heat exchangers, we offer our Temp-Plate® line of heat transfer surfaces.

Mueller Temp-Plate is an extremely versatile heat transfer surface that can be crafted into an almost unlimited number of styles and shapes. Temp-Plate's design provides highly efficient heat transfer performance. Its spot welded and inflated channels induce fluid turbulence to attain high heat transfer coefficients.

Call us for literature on Temp-Plate or to discuss how we can improve your entire heat transfer process.

Let Mueller Provide Your Heat Transfer Solution!



All products, specifications, and features listed herein are representative of the final product and are intended as reference only. We reserve the right to make alterations without notice.

## MUELLER

1600 West Phelps Street • Springfield, Missouri 65802, U.S.A. Phone: (417) 575-9000 • 1-800-MUELLER • Fax: (417) 575-9885 E-mail: heattransfer@paulmueller.com • www.paulmueller.com